




4515 East 139th Street
 Grandview, MO 64030
 (800) 362-9055
 Fax (800) 362-1463
 www.PRIER.com

C-134/234 Series Freezeless Wall Hydrant

Application

Original Heavy Duty Style

C-234 Loose Key Design



- Residential
- Freezeless
- Slim Seat
- Satin Nickel Plated



PRIER C-134 provides a year round source of water to areas of structures that are subject to freezing temperatures. The hydrant valve is connected to the supply piping in the heated portion of the structure, eliminating the possibility of freezing. Ordering the C-234 gives you the same style hydrant but with a vandal proof extended lockshield with operating key.

The PRIER C-134 is the original freezeless hydrant that is made in the same heavy pattern fashion that made it famous. It is available from stock in lengths from Close Coupled to 24". Longer sizes are available upon request.


Features

- C-UPC approved
- Integral cast flange with built-in drainage pitch
- Enclosed screw holes easily secure mounting screws
- Solid brass body, valve stem cap, seat and stem ends
- Satin nickel plated body maintains attractive finish
- Stainless steel seat washer screw and handle screw
- Powder coated cast aluminum handle
- Durable ACME threads secure stem at seat end
- Lock shield cap for stronger valve design
- AFG teflon with graphite packing for easy maintenance
- Standard "OO" size seat washer
- Spout aligning mark
- Slim seat inlet for easier installation

Inlet Styles



D Style
1/2" MIP x 1/2" SWT




S Style
1/2" SWT x 3/4" Push-On




X Style
1/2" Crimp PEX



W Style
1/2" Wirsbo® PEX



T Style
3/4" MIP x 1/2" FIP



F Style
3/4" MIP x 3/4" SWT



FX Style
3/4" Crimp PEX



FW Style
3/4" Wirsbo® PEX

Ordering

C-134D10

Operator

- 1- Handle Operated
- 2- Vandal Proof Lockshield

Inlet

- D- 1/2" MPT x 1/2" SWT
- F- 3/4" MPT x 3/4" SWT
- S- 1/2" SWT x 3/4" Push-On
- T- 3/4" MIP x 1/2" FIP
- W- 1/2" Wirsbo PEX®
- X- 1/2" Crimp PEX
- FX- 3/4" Crimp PEX
- FW- 3/4" Wirsbo PEX®


Length

- CC- Close Coupled
- 04- 4" Insertion
- 06- 6" Insertion
- 08- 8" Insertion
- 10- 10" Insertion
- 12- 12" Insertion
- 14- 14" Insertion
- 16- 16" Insertion
- 18- 18" Insertion
- 20- 20" Insertion
- 22- 22" Insertion
- 24- 24" Insertion
- XX- Special Size



4515 East 139th Street
 Grandview, MO 64030
 (800) 362-9055
 Fax (800) 362-1463
 www.PRIER.com

Replacement Parts



| ID | Part No. | Description |
|----|-------------|--|
| 1 | See Below | Stem Assembly, Contains: 1, 4 |
| 2 | 300-1008 | Valve Stem Cap |
| 3 | C-134KT-805 | Oval Handle and Screw Kit |
| 4 | C-134KT-802 | Seat Washer Replacement Kit (00 Beveled) |
| 5 | C-134KT-803 | Stem Packing Replacement Kit |
| 6 | 310-1015 | Valve Stem Cap for Loose Key |
| 7 | 390-1001 | Stem Packing Only |
| 8 | C-108KT-808 | Oval Style Key on Lanyard |
| | C-134KT-804 | Loose Key Conversion Kit Contains: 5, 6, 8 |
| | C-134KT-807 | C-134 Overhaul Kit Contains: 3, 4, 5 |

Replacement Stems



G Style Manufactured April 2013 - Present

| Part No. | Style | Description | Stem Length |
|------------|-------|---|--|
| P-231-11CC | G | Close Coupled Stem for C-134 Hydrant | 4 ³ / ₈ " OAL |
| P-231-1104 | G | Stem for 4" C-134 Hydrant | 6 ⁷ / ₈ " OAL |
| P-231-1106 | G | Stem for 6" C-134 Hydrant | 8 ⁷ / ₈ " OAL |
| P-231-1108 | G | Stem for 8" C-134 Hydrant | 10 ⁷ / ₈ " OAL |
| P-231-1110 | G | Stem for 10" C-134 Hydrant | 12 ⁷ / ₈ " OAL |
| P-231-1112 | G | Stem for 12" C-134 Hydrant | 14 ⁷ / ₈ " OAL |
| P-231-1114 | G | Stem for 14" C-134 Hydrant | 16 ⁷ / ₈ " OAL |
| P-231-1116 | G | Stem for 16" C-134 Hydrant | 18 ⁷ / ₈ " OAL |
| P-231-1118 | G | Stem for 18" C-134 Hydrant | 20 ⁷ / ₈ " OAL |
| P-231-1120 | G | Stem for 20" C-134 Hydrant | 22 ⁷ / ₈ " OAL |
| P-231-1122 | G | Stem for 22" C-134 Hydrant | 24 ⁷ / ₈ " OAL |
| P-231-1124 | G | Stem for 24" C-134 Hydrant | 26 ⁷ / ₈ " OAL |
| P-231-11US | G | *Universal Replacement Stem for C-134 Hydrant | Up to 16 ⁷ / ₈ " OAL |

****For the old style C-134 Series wall hydrant stems, see C-134 Series retired style spec sheet at www.PRIER.com. PRIER universal stems are replacement stems for any size from close coupled to 14." They require cutting the rod to proper length and soldering the brass stem end to the rod as directed in instructions.**